

SEARCHER 70

DX-073

DENTAL X-RAY



 Belmont®

Search for the quality and safety SEARCHER 70.

SEARCHER 70

DX-073



The powered-up Searcher 70, intraoral x-ray system provides optimum image quality and maximum diagnostic information with its advanced technology of microprocessor controlled mAs system.

Searcher 70 offset yoke and lines on the cone allow the operator to align the cone accurately each and everytime for reproducible quality film.

Compact lightweight scissor arm offers a superb flexibility, longer reach, perfect positioning and stability.

Specifications

Diagnostic x-ray equipment for dental use


Model	DX-073 SEARCHER 70
System	Simultaneous ignition, mAs system
Rated Line Voltage	100, 110, 120, 220, 230 or 240V as sepcified, 50/60Hz
Rated peak tube potential and rated tube current	70kVp 10mA
Effective focal point	0.8×0.8mm
Total Filtration	2.1mmAl
Cooling	Oil Cooling System
S.S.D.	200mm
Hand Switch	Deadman Type
Tubehead weight	7.8kgs

The manufacturers reserve the right to alter and improve the specification without notice.



Greater penetrating power of 70 kVp produces crisp and more anatomical detail in x-ray imaging.

Searcher 70 remains thin and reduces patient radiation exposure.



Searcher 70 control panel is designed for operating ease and cleaning ease with smooth pictographic selection switch panel. The hand exposure switch incorporates a safety feature.



DX-073 RK II
Room Type

Mobile Type
(DX-073 FM),
Floor Mount Type
(DX-073 FK1) &
Ceiling Mount Type
(DX-073 CK)
are also available.

 Belmont®

Printed in Japan 2005.02MA